




## Supplementary Materials: Corrosion Potential Modulation on Lead Anodes Using Water Oxidation Catalyst Coatings



**Figure S1.** Exemplary linear sweep voltammograms. Exemplary linear sweep voltammograms that were used for determining polarized dynamic equilibrium potentials in Table S1.

**Table S1.** Exchange current densities. Exchange current density for polarized dynamic equilibrium potentials, extrapolated from data in Figure S1.

Solution Additive	Polarized Eq. Jcorr (μA/cm²)
None	4.8
5 g/L Co <sup>2+</sup>	10.4
5 g/L Mn <sup>2+</sup>	0.38
Co-dppe	24.0